

AlcoStop Police Use Breathalyzer

4800

Fast & Rapid Alcohol Screening Device



Friendly
Advanced Technology



 Don't Drink Drive

Professional R&D and manufacturer of breathalyzers

InterMed



| | |
|--|---|
| Device: | |
| Measurement mode: | Scan Mode |
| Measurement range: | 0 to 100mg/100ml BAC |
| Sensitive: | |
| blowing distance(device to mouth)<5cm | ±5mg/100ml |
| blowing distance(device to mouth)5-10cm | ±6.0mg/100ml |
| blowing distance(device to mouth)>10cm | ±10mg/100ml |
| Pump: | Continuous extraction, speed >0.5L per minute |
| Ambient conditions: | |
| Operation temperature: | -5 °C ~ +50 °C |
| Storage temperature: | -30°C to + 70°C |
| Measurement time: | Minimum 1 second,adjustable |
| Ambient pressure: | 600 to 1400hPa |
| Ambient humidity | 20 to 98% r.h |
| Battery: | Li-ion rechargeable battery |
| Battery life: | More than 48 hours continuous working |
| Display: | Digital and full graphic backlight display |
| Alarm: | Red,yellow,green LED indication,alarm limit can be adjusted |
| Miscellaneous: | |
| Sensor: | Fuel cell |
| Sensor specificity | Alcohol only |
| Mouthpiece: | No need |
| Power save mode: | Automatic switch off after 2.5minutes without use |
| Calibration: | Every 12 months |